


| | | |
|------|--------------|------|
| MAPX | MODIFICATION | DATE |
| | | |



NOTES:
Housing: Thermoplastics
Contact: Copper Alloy
Shell: Copper Alloy/Steel
Voltage Current Rating:1.5 AMP. 30V AC
Insulation Resistance:1000MΩ Min.
Contact Resistance:30 MΩ Max.
Dielectric Withstanding Voltage:500W AC
Temperature Range:-55° C to +85° C
Insulator color: Black/White
Plastic material:PBT/LCP
Shell finish:Nickel plated/Tin-Lead plated
Contact finish:
01:Selective Gold Flash
02:Selective Gold 3U"
03:Selective Gold 5U"
04:Selective Gold 15U"
05:Selective Gold 30U"

| | | | | | | | | | |
|-------------------------------------|-------|------|-------|--------------|-----------|---------------|-------|--------------------------|---------------------|
| 产品图 PRODUCT CHART DWG | | | | 深圳市精拓金电子有限公司 | | | | | |
| 公差一览表 TOLERANCE UNLESS OTHERWISE | | | | 单位 UNITS | MM | 制图 DRAWING | Z-Y-B | 制图料号 PRODUCT PART NO. | 917-421A1018A40202 |
| X. | ±0.15 | X. | ±5° | 比例 SCALE | 1:1 | 审核 CHKD | | 产品名称 PRODUCT NO. | AM5代S款白胶焊线式+正面短路PIN |
| .XX | ±0.10 | .XX | ±2° | 日期 DATE | 2013.1.15 | 核准 APPD | | 角法 VIEW | ⊕ ◁ |
| .XXX | ±0.05 | .XXX | ±1° | | | | | 版本 VER | AO |
| | ±0.03 | | ±0.5° | | | | | | |