


1	2	3	4	5	6	7	8
REVISION		DESCRIPTION		DATE		DRAFTER	
A0		FIRST RELEASE		2020.02.25		Mark	



P2 OPEN 端
裁线图
RG178同轴电缆, 透明棕色双银线
P1 MMCX 端

技术要求:

- 1 装配要求: 见图面有备注说明。
- 2 方向要求: 无;
- 3 电气特性: 特性阻抗: 50Ω; 适用频率范围: DC-6GHz;
- 4 断短路与高压测试: 100%使用线材综合测试仪测试。
测试条件: 断短路判定值: 2kΩ; 直流导通电阻: 最大2.00Ω; 绝缘电阻: DC 300V, 0.05秒, 50MΩ。
- 6 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
- 7 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
- 8 包装规范: 20PCS/扎, 5扎/袋。
- 9 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

3	2TA025BK1-020	OD: 2.5*L20.0mm, 无卤阻燃, 125H2普通型, 黑色	1	---
2	MMCX-H481-001	MMCX 90度公头, FOR RG178 CABLE	1	YH-MX5505AD-01
1	2C5R17813BN1	RG178透明棕双银线-50 OHM	1	依裁线图裁线
No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS

GENERAL TOLERANCE: LINEAR: X ±0.20 X.X ±0.15 X.XX ±0.05 X.XXX ±0.01 ANGLE: X° ±4.00° X.X° ±3.00° X.XX° ±2.00° X.XXX° ±1.00°		HJ-Tech 东莞市皇捷通讯科技有限公司 手机: 15015262131/13714786106		
FILE NAME: 产品图	TITLE: 射频电缆组件			
ENG/DATE: Mark/20.02.25	RF CABLE, RG178透明棕双银线, P1端90度MMCX公头, P2端剥皮镀锡, 产品总长220mm			
CHE/DATE:	P/N: HJ-316-MMCX-L=220mm			
APP/DATE:	UNIT: mm	SCALE: 1:1	REVISION: A0	SHEET: 1/1

COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □ HF; □ SONY SS-00259; □ OTHERS H481
*NO USING ESTRICTED AND BANNED SUBSTANCE