





环保物料

TEL:0769-82001899

NOTES:
 Voltage Rating:250V AC/DC
 Current Rating:1.0A AC/DC
 Dielectric Withstand Voltage:500V AC/minute
 Contact Voltage:20M Max.
 Insulation Voltage:1000M Min
 Operation temperature:-40 °C to +105 °C
 Insulator Material:Polyester.UL94V-0
 Contact Material:Brass
 Contact Plating:AuorSn Plated on Nickel Overall



Recommended P.C.B Layout
 P.C.B Board Tolerance±0.05



				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	±0.30	X°	±5°			CHKD	DATE
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	1.27mm Female Header Connectors	
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	PM127V-11-xx-H46	
				.XXX	±0.03	.XXX°	±0.5°			SCALE	1:1
				AO	MODIFICATION	DRAW	DATE			DWG. NO.	009