



PCB LAYOUT

型号: KH-A2001WF-02A

SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon 6T, UL94V-0
PIN Brass Tin-plated
Solder tad Brass Tin-plated

编 号	尺寸 (mm)		
	A	B	C
A2001WF-02A	2.00	8.00	6.70
A2001WF-03A	4.00	10.00	8.70
A2001WF-04A	6.00	12.00	10.70
A2001WF-05A	8.00	14.00	12.70
A2001WF-06A	10.00	16.00	14.70
A2001WF-07A	12.00	18.00	16.70
A2001WF-08A	14.00	20.00	18.70
A2001WF-09A	16.00	22.00	20.70
A2001WF-10A	18.00	24.00	22.70
A2001WF-11A	20.00	26.00	24.70
A2001WF-12A	22.00	28.00	26.70
A2001WF-16A	30.00	36.00	34.70

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生 2013、07、01	料号 PART NO.	版本 REV.	A
			.X±0.25	.X'±2'					
			.X±0.20	.X'±1'	审核 CHECK	张名 2013、07、03	品名 TITLE	PH贴片 WAFER SMT TYPE	页次 SHEET
			.XX±0.15	.XX'±0.5'	核准 APPROVAL	张名 2013、07、05	客户料号 CUTM. NO.		1/1
			.XXX±0.10	.XXX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1	

深圳市金航标电子有限公司

WWW.BDS666.COM 0755-83044319