



PCB LAYOUT

型号: KH-A2001WF-05A

SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon 6T, UL94V-0
PIN Brass Tin-plated
Solder tad Brass Tin-plated

编号	尺寸 (mm)		
	A	B	C
A2001WF-02A	2.00	8.00	6.70
A2001WF-03A	4.00	10.00	8.70
A2001WF-04A	6.00	12.00	10.70
A2001WF-05A	8.00	14.00	12.70
A2001WF-06A	10.00	16.00	14.70
A2001WF-07A	12.00	18.00	16.70
A2001WF-08A	14.00	20.00	18.70
A2001WF-09A	16.00	22.00	20.70
A2001WF-10A	18.00	24.00	22.70
A2001WF-11A	20.00	26.00	24.70
A2001WF-12A	22.00	28.00	26.70
A2001WF-16A	30.00	36.00	34.70

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	版本 REV.	A
			$X \pm 0.25$	$X' \pm 2'$		2013. 07. 01	审核 CHECK			
			$.X \pm 0.20$	$.X' \pm 1'$	2013. 07. 03	核准 APPROVAL	张名	客户料号 CUTM. NO.		
			$.XX \pm 0.15$	$.XX' \pm 0.5'$	2013. 07. 05	单位 UNITS	MM	比例 SCALE	1:1	
			$.XXX \pm 0.10$	$.XXX' \pm 0.5'$				深圳市金航标电子有限公司		
								WWW.BDS666.COM	0755-83044319	