



型号: KH-A1001LF-02A

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer Nylon 6T, UL94V-0
PIN Phosphoric bronze Tin-plated
Solder tad Phosphoric bronze Tin-plated



PCB LAYOUT

| 编 号 | 尺寸 (mm) | | |
|-------------|---------|-------|-------|
| | A | B | C |
| A1001LF-02A | 1.00 | 4.00 | 3.20 |
| A1001LF-03A | 2.00 | 5.00 | 4.20 |
| A1001LF-04A | 3.00 | 6.00 | 5.20 |
| A1001LF-05A | 4.00 | 7.00 | 6.20 |
| A1001LF-06A | 5.00 | 8.00 | 7.20 |
| A1001LF-07A | 6.00 | 9.00 | 8.20 |
| A1001LF-08A | 7.00 | 10.00 | 9.20 |
| A1001LF-09A | 8.00 | 11.00 | 10.20 |
| A1001LF-10A | 9.00 | 12.00 | 11.20 |
| A1001LF-11A | 10.00 | 13.00 | 12.20 |
| A1001LF-12A | 11.00 | 14.00 | 13.20 |
| A1001LF-20A | 19.00 | 22.00 | 21.20 |

| 制图 DRAWN | 变更内容 DESCRIPTION | 日期 DATE | GENERL TOLERANCE | | 制图 Mapping | 料号 PART NO. | 版本 REV. |
|-------------|---------------------|------------|------------------|------------|------------------------|--|------------|
| | | | X±0.25 | .X*2° | 钱岳生 2013、07、01 | KHA1001LF-NA | A |
| | | | .X±0.20 | .X*1° | 审核 张名 2013、07、03 | 品名 1.0立贴 TITLE WAFER SMT TYPE | 页次 1/1 |
| | | | .XX±0.15 | .XX*±0.5° | 核准 张名 2013、07、05 | 客户料号 CUTM. NO. | |
| | | | .XXX±0.10 | .XXX*±0.5° | 单位 MM | 比例 SCALE | 1:1 |
| | | | | | | 深圳市金航标电子有限公司 | |
| | | | | | | WWW.BDS666.COM 0755-83044319 | |