



型号: KH-A1001WF-04A

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer Nylon 6T, UL94V-0
PIN Phosphoric bronze Tin-plated
Solder tad Phosphoric bronze Tin-plated

编 号	尺寸 (mm)		
	A	B	C
A1001WF-02A	1.00	4.00	3.20
A1001WF-03A	2.00	5.00	4.20
A1001WF-04A	3.00	6.00	5.20
A1001WF-05A	4.00	7.00	6.20
A1001WF-06A	5.00	8.00	7.20
A1001WF-07A	6.00	9.00	8.20
A1001WF-08A	7.00	10.00	9.20
A1001WF-09A	8.00	11.00	10.20
A1001WF-10A	9.00	12.00	11.20
A1001WF-11A	10.00	13.00	12.20
A1001WF-12A	11.00	14.00	13.20
A1001WF-20A	19.00	22.00	21.20

PCB LAYOUT

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 Mapping	钱岳生 2013.07.01	料号 PART NO.	KHA1001WF-NA	版本 REV.	A
			X.±0.25	X.*±2'	审核 Audit	张名 2013.07.03	品名 TITLE	1.0贴片 WAFER SMT TYPE	页次 SHEET	1/1
			.X±0.20	.X*±1'	核准 Approved	张名 2013.07.05	客户料号 CUTM. NO.			
			.XX±0.15	.XX*±0.5'	单位 Units	MM	比例 SCALE	1:1	深圳市金航标电子有限公司	
			.XXX±0.10	.XXX*±0.5'			WWW.BDS666.COM	0755-83044319		