



型号: KH-A1251WF-04A

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $100\text{M}\Omega$ Min
- 6、Withstanding Voltage: 500V AC/minute
- 7、Material: Wafer Nylon46, UL94V-0
PIN Brass Tin-plated
Solder tad Brass Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
A1251WF-02A	1.25	7.35
A1251WF-03A	2.50	8.60
A1251WF-04A	3.75	9.85
A1251WF-05A	5.00	11.10
A1251WF-06A	6.25	12.35
A1251WF-07A	7.50	13.60
A1251WF-08A	8.75	14.85
A1251WF-09A	10.00	16.10
A1251WF-10A	11.25	17.35
A1251WF-11A	12.50	18.60
A1251WF-12A	13.75	19.85
A1251WF-20A	23.75	29.85

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生 2013、07、01	料号 PART NO.	KHA1251WF-NA	版本 REV.	A
			X.±0.25	X.'±2'	审核 CHECK	张名 2013、07、03	品名 TITLE	1.25贴片 WAFER SMT TYPE	页次 SHEET	1/1
			.X±0.20	.X'±1'	核准 APPROVAL	张名 2013、07、05	客户料号 CUTM. NO.			
			.XX±0.15	.XX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1		
			.XXX±0.10	.XXX'±0.5'	深圳市金航标电子有限公司 WWW.BDS666.COM 0755-83044319					