






SIGN	DATE	DESCRIPTION	APPROVER
△	11.30	NEW PRODUCT ISSUE	nierzhenqi
△			
△			



SPECIFICATIONS:
 Current rating: 1.0A AC, DC
 Voltage rating: 250V AC, DC MAX
 Contact resistance: 20m Ω MAX
 Insulation resistance: 500M Ω MIN
 Withstanding voltage: 500V AC/minute
 Temperature range: -25°C to +105°C

MATERIAL:
 Insulator: PBT UL94V-0
 Contact: Brass.
 Finish: Gold Flash.

PIN	A±0.25	B±0.15	C±0.25
8	14.86	7.62	14.86
10	17.40	10.16	17.40
14	22.48	15.24	22.48
16	25.02	17.78	25.02
18	27.56	20.32	27.56
20	30.10	22.86	30.10
24	35.18	27.94	35.18
26	37.72	30.48	37.72
30	42.80	35.56	42.80
34	47.88	40.64	47.88
40	55.50	48.26	55.50
50	68.20	60.96	68.20
60	80.90	73.66	80.90
64	85.98	78.74	85.98

810-XX10-012-X000

Number of Positions
10~64

Relief type
 1: W/O Strain Relief
 2: W/Strain Relief

Insulator color
 1: Black
 3: White
 4: Grey

nexttron 正凌精密工业股份有限公司
 NEXTRONICS ENGINEERING CORP

PART. NAME: xxPIN 2.54mm IDC CONNECTOR				TITLE: 2.54mm IDC CONNECTOR	
PART. NO.: SEE TABLE				DWG NAME: 810-5010-012-4000	
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:	Tolerance
jeff	jeff		nierzhenqi		x. ±0.50
				UNITS: mm	x.x ±0.20
				SCALE:	x.xx ±0.10
				REVISION:	xx* ±1*