




RoHS

SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Dimension antitheses list				
ITEM	H	D	W	
Alternate	13.0	0.10	8.20	

深圳市连盛精密连接器有限公司

PART NO. **FH-00372---A0001**

TITLE: 2.54FH 3H=8.5+1.5+2.5 2x20P SMT
 W5.0mm L=13.5

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30			UNIT			
X.XX	±0.20	CHECK		mm	A4		
X.XXX	±0.10			SIZE	1/1		
Angle	±3°	APPROVE		SHEET	1/1		
DIM	TOL			PROJ.	☐		

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.10.08	NEW DRAWING	
1			