





# ROHS

## SPECIFICATIONS

Rated Current: 1.5AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 500V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°c to +105°c  
 Contact Material: Brass  
 Contact Plating: Au Over Ni  
 Insulator Material: Polyester(UL94V-0)  
 Standard: PA6T  
 Max. Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30			UNIT	mm			SIZE	A4
X.XX	±0.20	CHECK		SHEET	1/1	TITLE:		2.0FH H4.3mm 2x20pin 180° W4.50	PC2.8
X.XXX	±0.10	APPROVE		PROJ.		TITLE:			
Angle	±3°					TITLE:			
DIM	TOL					TITLE:			
REV	DATE	MODIFICATION DESCRIPTION		CHANGE		TITLE:			
1						TITLE:			
2						TITLE:			
3						TITLE:			
4						TITLE:			
5						TITLE:			
6						TITLE:			
7						TITLE:			
8						TITLE:			
9						TITLE:			