

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass

Contact Plating:Au Over Ni



Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)

(PCB BOARD TOLERANCE±0.05)



				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司	
				X.X	±0.30			UNIT	mm				
				X.XX	±0.20	CHECK		SIZE	A4	PART NO.		FH-00512	
A0	2012.07.23	NEW DRAWING		X.XXX	±0.10	APPROVE		SHEET	1/1	TITLE:		2.0FH H=4.3 W=4.5 2*45P DIP PC2.8 O型 AU1U 青铜 PA6T 带凸(凸高1.0mm) 带单边柱 Φ0.8 H1.0	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM			TOL	PROJ.				