





SPECIFICATIONS

Rated Current: 1.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact Plating: Au 3U Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)



Dimension antitheses list				
ITEM	PA	PC	L	
Standard	6.30	3.00	11.0	
Alternate				

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30	Y.YuSheng	12.03.28	UNIT	mm	SIZE	A4
X.XX	±0.20	CHECK		SHEET	1/1	SHEET	1/1
X.XXX	±0.10	APPROVE		PROJ.			
Angle	±3°						
DIM	TOL						

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.03.28	NEW DRAWING	
1			

PART NO. PH-00205---A0001

TITLE: 2.54PH H=1.7 2X20P DIP PA6.3 PC3.0 L=11.0