





RoHS

SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°c to +105°c
 Contact Material: Brass
 Contact Plating: Au Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 5 seconds)



Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	6.00	3.50	7.00	11.20
Alternate				

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.		
X.X	±0.30			UNIT	mm			PH-00603 ---A0001		
X.XX	±0.20	CHECK		SIZE	A4			TITLE:		
X.XXX	±0.10			SHEET	1/1			2.54Pin H=2.5 2*15P SMT=7.0 PA6.0 PB3.5		
Angle	±3°	APPROVE		PROJ.	1/1			L=11.2 AU0.8U PA6T 铆柱 柱子在2-3排和1.3-1.4排之间		
DIM	TOL							φ1.6 H=2.0		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE							
1	2012.04.11	NEW DRAWING								

Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)