





# RoHS

## SPECIFICATIONS

Rated Current: 3.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°c to +105°c  
 Contact Material: Brass  
 Contact Plating: Au Over Ni  
 Insulator Material: Polyester (UL94V-0)  
 Standard: PA6T  
 Max. Processing Temp: 230°C for 30-60 seconds  
 (260°C for 5 seconds)



Recommended P.C.B Layout (Top Side)  
 (PCB BOARD TOLERANCE  $\pm 0.05$ )



Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	6.00	3.20	8.00	11.30
Alternate				

深圳市连盛精密连接器有限公司

A

OPERATION	DRAW	SCALE	FIT	PART NO.
X.X		UNIT	mm	PH-00668---A0001
X.XX	CHECK	SIZE	A4	
X.XXX		SHEET	1/1	TITLE: 2.54PH 2x4pin H2.5mm SMT
Angle	APPROVE	PROJ.		
DIM				

B

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.04.11	NEW DRAWING	
1			

C

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
1			

D

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
1			

E

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
1			

F

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
1			

G

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
1			