


RoHS




SPECIFICATIONS

Rated Current:1.5AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Au or Sn Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 5 seconds)



Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list					
ITEM	PA	D	PB	W	L
Alternate	5.30	0	3.50	6.50	10.50

				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司 PART NO. A0001-PH-00914 TITLE: 2.0PH 2x13pin 2H=2X1.5mm SMT	
				X.X	±0.30			UNIT	mm				
				X.XX	±0.20	CHECK		SIZE	A4				
A0				2012.04.11	NEW DRAWING			SHEET	1/1				
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE		PROJ.	☛				
1	2	3	4	5	6	7	8	9					