


**RoHS**




**SPECIFICATIONS**

Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list				
ITEM	PA	PB	PC	L
Standard	10.0	3.90	3.00	17.50
Alternate				

**深圳市连盛精密连接器有限公司**

PART NO. PH-00922

TITLE: 2.54PH H=2.5 1X10P 反弯 PA10.0 PB3.9 PC3.0 L=17.5 AU0.8U PA6T

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	SCALE	FIT
				DIM	TOL			
A0	2012.03.28	NEW DRAWING		X.X	±0.30		UNIT	mm
				X.XX	±0.20	CHECK	SIZE	A4
				X.XXX	±0.10		SHEET	1/1
				Angle	±3'	APPROVE	PROJ.	◆