





RoHS

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



				OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		
				X.X	±0.30		UNIT	mm			
				CHECK		APPROVE	SIZE	A4	PART NO.	PH-00993	
A0	2012.03.28	NEW DRAWING		X.XXX	±0.10		SHEET	1/1	TITLE:	2.54PH 2H=2X2.5 2X3P DIP PA=PC=3.0 PB16.4 L=22.4 AU0.8U PA6T	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	PROJ.					