





RoHS

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



				OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30		UNIT	mm		
				CHECK		APPROVE	SIZE	A4	PART NO. PH-01016	
A0	2012.03.28	NEW DRAWING		X.XXX	±0.10		SHEET	1/1	TITLE: 2.54PH 2H=2x2.5 2X13P DIP PA6.0 PB19.0 PC3.0 L=28.0 PA6T	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	PROJ.				