





RoHS

SPECIFICATIONS

Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°c to +105°c

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)



Dimension antitheses list				
ITEM	PA	PB	PC	L
Standard	6.00	4.30	3.00	13.80
Alternate				

OPERATION		DRAW	SCALE	FIT
X.X	±0.30		UNIT	mm
X.XX	±0.20	CHECK	SIZE	A4
X.XXX	±0.10		SHEET	1/1
Angle	±3°	APPROVE	PROJ.	☉
DIM	TOL			

深圳市连盛精密连接器有限公司

PART NO.	PH-01230
TITLE:	2.54PH 2.5mm 1X40 90°正弯

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.07.02	NEW DRAWING	