





**SPECIFICATIONS**

Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°c to +105°c



Contact Material:Brass  
 Contact Plating:Au or Sn Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)



**Ordering Information**

3210 XX R XX X B K00 X 02

- No. of Pins 6---64
- Contact Plating G0:Gold Flash G1:3U" Gold G2:5U" Gold G3:10U" Gold G4:15U" Gold G5:30U" Gold S0:Gold Flash/Tin
- Insulator Material Option A=BK-PBT B=BK-PA66 C=BK-PA6T D=BK-PA46 E=BK-PA9T F=BK-LCP
- Packing T=Tube A=Tray P=Tube+Cap



料号 : 40-004642-000-R002

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X		±0.30		YTuSheng		17.06.01		BH-00080---A0006	
X.XX		±0.20		CHECK		UNIT		mm	
X.XXX		±0.10		APPROVE		SIZE		A4	
Angle		±3°		SHEET		1/1		TITLE:	
DIM		TOL		PROL.		◆		2.54mm Box Header H8.8mm 90°	
L=14.8/L=19.8		TOP							

深圳市连盛精密连接器有限公司

1	2	3	4	5	6	7	8	9
REV	DATE	MODIFICATION DESCRIPTION	CHANGE					
A	2017.06.01	NEW DRAWING						