





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C
 Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list				
ITEM	H	D	W	L
Alternate	19.00	0.10	8.20	20.80

深圳市连盛精密连接器有限公司

PART NO.

BH-00085---A0001

TITLE:

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30	X.X	CHECK	UNIT	mm	PROJ.	
X.XX	±0.20	X.XX	CHECK	SIZE	A4		
X.XXX	±0.10	X.XXX	CHECK	SHEET	1/1		
Angle	±3°	APPROVE					
DIM	TOL						

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.03.28	NEW DRAWING	
1			