


RoHS

SPECIFICATIONS

Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:400V AC/DC
 Insulation Resistance:800MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



料号 : T.JC.01.Y020900002

深圳市连盛精密连接器有限公司

				OPERATION		DRAW		SCALE		FIT		PART NO. BH-00164	
				X.X ±0.30				UNIT		mm			
				X.XX ±0.20		CHECK		SIZE		A4		TITLE: 2.0BOX 90P H=5.65 W=7.0 DIP PC2.8 L=8.2 AU0.8U PA6T 黑色 带外大小柱 改模后 两端壁厚加0.65mm	
A0		2018.09.27		X.XXX ±0.10		APPROVE		SHEET		1/1			
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM	TOL	APPROVE	PROJ.					