




**Technical Specs:**

**Insulator:** Black glass filled polyester PPS-GF30-FR  
**Flammability:** UL 94V-0  
**Sleeve:** Brass  
**Contact clip(4/6 finger):** Beryllium copper(C17200)  
**Accepted pin:** Ø0.38 to 0.56mm  
**Forces:** (polished steel gauge Ø0.43mm)  
 --Insertion 2 N typ  
 --Withdrawal 1 N typ  
**Mechanical life:** min500 cycles  
**Rated current:** 3A  
**Contact resistance:** max 10mΩ  
**Dielectric resistance:** Min 1000MΩ  
**Operating temperature:** -40°C to +105°C  
**Soldering temperature:** 260°C, 10s max



料号：FH-00306

深圳市连盛精密连接器有限公司

PART NO. FH-00306

TITLE: 2.54X1.9圆孔排母 1x3p

OPERATION		DRAW		SCALE		FIT		PART NO.	
		DRAW		UNIT	mm			FH-00306	
X.X	±0.30								
X.XX	±0.20	CHECK							
X.XXX	±0.10			SIZE		A4			
Angle	±3°			SHEET		1/1			
DIM	TOL	APPROVE		PROJ.					
CHANGE									
REV	DATE	MODIFICATION DESCRIPTION						TITLE:	
A0	2012.08.08	NEW DRAWING						2.54X1.9圆孔排母 1x3p	