




SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact Plating: Au Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PBT
 Max. Processing Temp: 180°C for 30-60 seconds
 (200°C for 10 seconds)



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE	FIT	PART NO.	
X.X	±0.30	X.X	±0.30	UNIT	mm	SIZE	A4
X.XX	±0.20	X.XX	±0.20	CHECK		SHEET	1/1
X.XXX	±0.10	X.XXX	±0.10	ANGLE	±3°	PROJ.	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	TITLE:
A0	2012.03.28	NEW DRAWING					BH-00017 --- A0001
1							2.54BOX H8.8mm 30P 180°