


RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c
 Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



深圳市连盛精密连接器有限公司

PART NO. BH-00023---A0006

TITLE: 2.54BOX H8.8mm 16P SMT

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW		SCALE		FIT	PART NO.	TITLE:
				X.XX	±0.30	CHECK	UNIT	mm				
A0	2012.03.28	NEW DRAWING		X.XX	±0.20			SIZE	A4		BH-00023---A0006	
				X.XXX	±0.10			SHEET	1/1			
				Angle	±3°	APPROVE		PROJ.				
1				DIM	TOL							