



SPECIFICATIONS

Current Rating: Lamps
 Insulator Resistance: 5000Megohms min.
 Dielectric Withstanding: AC 500v
 Operating Temperature: -40°C ~ +105°C
 Contact Material: phosphor Bronze
 Insulator Material: PA6T
 Finish: Gold flash

UNSPECIFIED TOLERANCE: ± 0.20

Dimensions list

Contacts Per row	Dimensions		Contacts Per row	Dimensions	
	A	B		A	B
1	2.5	0	21	42.5	40.0
2	4.5	2.0	22	44.5	42.0
3	6.5	4.0	23	46.5	44.0
4	8.5	6.0	24	48.5	46.0
5	10.5	8.0	25	50.5	48.0
6	12.5	10.0	26	52.5	50.0
7	14.5	12.0	27	54.5	52.0
8	16.5	14.0	28	56.5	54.0
9	18.5	16.0	29	58.5	56.0
10	20.5	18.0	30	60.5	58.0
11	22.5	20.0	31	62.5	60.0
12	24.5	22.0	32	64.5	62.0
13	26.5	24.0	33	66.5	64.0
14	28.5	26.0	34	68.5	66.0
15	30.5	28.0	35	70.5	68.0
16	32.5	30.0	36	72.5	70.0
17	34.5	32.0	37	74.5	72.0
18	36.5	34.0	38	76.5	74.0
19	38.5	36.0	39	78.5	76.0
20	40.5	38.0	40	80.5	78.0

APPROVALS		DATE			
DRAWN	ZHIWEI, CHEN	2015.07.07			
CHECKED				TITLE: PH2.0*4.3 180° 排母	
APPROVALS				PART NO. GP25-2021WV-NP	
TOLERANCES ARE		30~0.15	±0.30	ANGLE	UNIT: mm
		10~30	±0.20	±2°	SCALE: 1:1
		5~10	±0.15		PROJ.
		~5	±0.10		SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.
	A		NEW		