




2.54 ± 0.15



2.54 ± 0.15



Specifications
 Current Rating: 3 Ampere
 Insulation Resistance: 1000M Min.
 Dielectric Withstanding: 500V AC
 Contact Resistance: 20m Max.
 Operating Temperature: -40° C to +105° C
Materials
 Contact Material: Brass
 Contact Plating: Au or Sn over 50U" Nickel
 Insulator : Glass Filled Polyester (UL 94V-0)
 PBT Black



APPROVALS		DATE		TITLE:	
DRAWN	ZHIWEI.CHEN	2015.07.07		GP26-2520WV-NP	
CHECKED				PART NO.	
APPROVALS				UNIT: mm	
TOLERANCES ARE		30 ^{±0.15}	±0.30	ANGLE	SCALE: 1:1
		10 ^{±0.10}	±0.20		PROJ.
		5 ^{±0.10}	±0.15	±2°	SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.
	A		NEW		APPRO.

