




POLES	PART NO	DIMENSION(S)(mm)	
		A	B
2	2	2.0	6.1
3	3	4.0	8.1
4	4	6.0	10.1
5	5	8.0	12.1
6	6	10.0	14.1
7	7	12.0	16.1
8	8	14.0	18.1
9	9	16.0	20.1
10	10	18.0	22.1
11	11	20.0	24.1
12	12	22.0	26.1
13	13	24.0	28.1
14	14	26.0	30.1
15	15	28.0	32.1
16	16	30.0	34.1



■ 技术参数 (SPECIFICATIONS)

- ◆ 额定电压: 250V AC/DC
- ◆ Voltage rating: 250V AC/DC
- ◆ 额定电流: 2.0A AC/DC MIN
- ◆ Current rating: 2.0A AC/DC MIN
- ◆ 耐压值: 800V AC/minute
- ◆ Withstand voltage 800V AC/minute
- ◆ 绝缘电阻: 1000MΩ MIN
- ◆ Insulation resistance: 1000MΩ MIN
- ◆ 接触电阻: 20mΩ MAX
- ◆ Contact resistance: 20mΩ MAX
- ◆ 工作温度: -25°C ~ +85°C
- ◆ Working Temperature: -25°C ~ +85°C
- ◆ 间距: 2.0 mm
- ◆ Pitch: 2.0 mm

■ 材料 (MATERIAL)

- ◆ 外壳: 尼龙66
- ◆ Housing: PA66
- ◆ 插针: 黄铜
- ◆ Pin: Brass

APPROVALS		DATE	TITLE:	
DRAWN	ZHIWEI, CHEN	2015.07.07	GP01-2001WR-NP	
CHECKED				
APPROVALS				
TOLERANCES ARE		30~0.1±	±0.30	ANGLE
		10~0.30	±0.20	UNIT: mm
		5~0.10	±0.15	SCALE: 1:1
		~ 5	±0.10	PROJ.
			±2'	DRAWING NO. _____
ECN NO.	REV.	DATE.	DESCRIPTION.	SHEET 1 OF 1
	A		NEW	

