






Poles	DIM A	DIM B	DIM C
2P	4.25	1.25	7.3
3P	5.50	2.50	8.5
4P	6.75	3.75	9.8
5P	8.00	5.00	11.0
6P	9.25	6.25	12.3
7P	10.50	7.50	13.5
8P	11.75	8.75	14.8
9P	13.00	10.00	16.0
10P	14.25	11.25	17.3
11P	15.50	12.50	18.5
12P	16.75	13.75	19.8
13P	18.00	15.00	21.0
14P	19.25	16.25	22.3
15P	20.50	17.50	23.5
16P	21.75	18.75	24.8



■ 技术参数 SPECIFICATIONS

- ◆ 适用线规: AWG.#28~#32
- ◆ Applicable Wire: AWG.#28~#32
- ◆ 额定电压: 125V DC/AC(rms)
- ◆ Rated voltage: 125V DC/AC(rms)
- ◆ 额定电流: 1A (AWG.#28)
- ◆ Rated Current: 1A (AWG.#28)
- ◆ 耐压值: 250V AC/minute
- ◆ Withstand voltage: 250V AC/min.
- ◆ 工作温度: -40°C ~ +85°C
- ◆ Working Temp: -40°C ~ +85°C
- ◆ 绝缘电阻: ≥100 MΩ
- ◆ Insulation resistance: ≥100 MΩ
- ◆ 接触电阻: ≤20 mΩ
- ◆ Contact resistance: ≤20 mΩ
- 材料 MATERIAL
- ◆ 绝缘体: 尼龙9T, UL94-V0
- ◆ Insulator: PA9T, UL94-V0
- ◆ 接触针: 磷铜
- ◆ Contact PIN: Phosphor bronze
- ◆ 焊片: 磷铜
- ◆ Solder tab: Phosphor bronze

APPROVALS		DATE	TITLE:	
DRAWN	ZHWEI,CHEN	2017.09.13	1.25mm SMT 卧式	
CHECKED			PART NO. GP01-1250WRS-NP	
APPROVALS			UNIT: mm	SCALE: 1:1
TOLERANCES ARE				PROJ.
	30~0.1mm	±0.30		
	10~30	±0.20		
	5~10	±0.15		
	~5	±0.10		
ANGLE		±2'	DRAWING NO.	SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.	
	A		NEW	

GEPU 歌普