



**SPECIFICATIONS**  
 Current Rating: 1A AC,DC  
 Voltage Rating: 125V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 20mΩ Max.  
 Insulation Resistance: 100MΩ Min.  
 Withstanding Voltage: 500V AC/minute  
 Pin Material: Phosphor Bronze/Tin-plated

Ordering Information & Dimensions

Circuit No.	Dimensions		Circuit No.	Dimensions	
	A	B		A	B
02P	1.25	4.25	11P	12.50	15.50
03P	2.50	5.50	12P	13.75	16.75
04P	3.75	6.75	13P	15.00	18.00
05P	5.00	8.00	14P	16.25	19.25
06P	6.25	9.25	15P	17.50	20.50
07P	7.50	10.50	16P	18.75	21.75
08P	8.75	11.75	17P	20.00	23.00
09P	10.00	13.00	18P	21.25	24.25
10P	11.25	14.25			

APPROVALS		DATE	
DRAWN	ZHIWEI, CHEN	2015.07.07	
CHECKED		TITLE:	
APPROVALS		PART NO.	
TOLERANCES ARE		SCALE: 1:1	
30~0.15	±0.30	ANGLE	PROJ.
10~0.30	±0.20	UNIT: mm	
5~10	±0.15	DRAWING NO.	SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.
	A		NEW



GP01-1250V-NP