





MAPX	MODIFICATION	DATE



NOTES:

- Housing: Thermoplastics
- Contact: Copper Alloy
- Shell: Copper Alloy/Steel
- Voltage Current Rating: 1.5 AMP. 30V AC
- Insulation Resistance: 1000MΩ Min.
- Contact Resistance: 30 MΩ Max.
- Dielectric Withstanding Voltage: 500W AC
- Temperature Range: -55° C to +85° C
- Insulator color: Black/White
- Plastic material: PBT/LCP
- Shell finish: Nickel plated/Tin-Lead plated
- Contact finish:
  - 01: Selective Gold Flash
  - 02: Selective Gold 3U"
  - 03: Selective Gold 5U"
  - 04: Selective Gold 15U"
  - 05: Selective Gold 30U"

<b>产品图</b> PRODUCT CHART DWG				<b>深圳市精拓金电子有限公司</b>							
公差一览表 TOLERANCE UNLESS OTHERWISE				单位	MM	制图	尹先华	制图料号	917-161B101AAX0220		
X	±0.25	X	±5.°	UNITS		DRAWING		PRODUCT PART NO.			
.X	±0.20	.X	±2.°	比例	1:1	审核	郭志富	产品名称	AM E款一体式双卡点右边短路		
.XX	±0.15	.XX	±1.°	SCALE		CHKD		PRODUCT NO.	铁壳反向PBT白胶E款端子17MM 得康		
.XXX	±0.10	.XXX	±0.5°	日期	2015.01.14	核准	黄国荣	角法	角法	版本	AO
				DATE		APPD		VIEW	角法	VER	