


COIL: @ +25 °C
 RESISTANCE 400 OHMS ± 10%
 NOMINAL VOLTAGE 24.0 VDC
 MUST OPERATE 17.0 VDC
 MUST RELEASE 1.4 VDC

ENVIRONMENT:
 VIBRATION 10 CPS TO 500 CPS @ 10 g's
 SHOCK 30 g's 6 MS. DURATION
 TEMPERATURE -55 °C TO +125 °C

NOTES: OPERATE TIME 5 MS MAX.
RELEASE TIME 3 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 5A 30 VDC
RESISTIVE 100,000 OPERATIONS

DR. R.B. 7/24/92 CK. 7/24/92



CUST. HI-G
 CUST. NO. FS5-2A-124P

TYPE **HFW5A RELAY**

HFW5A1201S501