





环保要求 RoHS 2.0




NOTES:  
 1.MATERIAL:  
 HOUSING:THERMOPLASTIC(UL94V-0) NATURE  
 ACTUATOR:THERMOPLASTIC(UL94V-0) BLACK  
 TERMINAL:PHOSPHOR BRONZE PLATED GOLD 1u" FOR SOLDERING AREA AND CONNECT AREA, PLATED NI MIN 30u" FOR ALLOVER UNDER.  
 FITTING NAIL:PHOSPHOR BRONZE MATTE TIN MIN 80u" PLATED FOR ALLOVER PLATED NI MIN 30u" FOR ALLOVER UNDER.  
 2.SPECIFICATION  
 CURRENT RATING: 0.5A 50VAC/DC  
 CONTACT RESISTANCE: 40mΩ MAX  
 INSULATION RESISTANCE: 100MΩ MIN AT 500V DC  
 OPERATING TEMPERATURE RANGE: -25°C TO +85°C  
 WITHSTANDING VOLTANG: 500V AC/minute




RECOMMENDED FFC DIM. WITH LOCK



RECOMMENDED FFC DIM WITHOUT LOCK



SECTION A-A SCALE 2:1



P.C.B LAYOUT REF

料号	Pin数(N)	A	B	C
AFC18-S80FIA-00	80	44.1	39.50	40.60
深圳市钜硕电子有限公司 SHENZHEN JUSHUO ELECTRONIC CO.,LTD		产品料号: AFC18-S80FIA-00		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	APPROVED BY	DATE	TITLE	
XX ±0.30	CHECKED BY	DATE	FPC CONN. 0.5P H1.8 FLIP TYPE 成品图	
XXX ±0.20	DRAWN BY	DATE	DOCUMENT NO	PAGE 1
X.XXX ±0.10	UNIT	SIZE	DRAWING NO	REV A
ANG ±0°30'	MM	A4	SHEET 1/1	SCALE 1:1
TION	CHK	DATE		