




# ROHS

## SPECIFICATIONS

Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°c to +105°c  
 Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30	CHECK		UNIT	mm	A4		PH-01162	
X.XX	±0.20	CHECK		SIZE	A4	1/1		2.54PH 2H=2x2.5 2X18P DIP PA7.0	
X.XXX	±0.10	CHECK		SHEET	1/1	1/1		PB14.0 PC3.0 L=24.0 PA6T	
Angle	±3°	APPROVE		PROJ.	◆	1/1			
DIM	TOL								
OPERATION		DRAW		SCALE		FIT		PART NO.	
DRAW		CHECK		UNIT		mm		PH-01162	
CHECK		CHECK		SIZE		A4		2.54PH 2H=2x2.5 2X18P DIP PA7.0	
CHECK		CHECK		SHEET		1/1		PB14.0 PC3.0 L=24.0 PA6T	
APPROVE		APPROVE		PROJ.		◆			
APPROVE		APPROVE							

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.03.28	NEW DRAWING	

1	2	3	4	5	6	7	8	9
---	---	---	---	---	---	---	---	---