




P.C.B LAYOUT(copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																																																																
	A		NEW																																																																			
<table border="1"> <tr> <td>② Terminal</td> <td>3</td> <td>Phosphor bronze</td> <td>Au Plating</td> </tr> <tr> <td>① Housing</td> <td>1</td> <td>Nylon</td> <td>Black</td> </tr> <tr> <td>ITEM</td> <td>PART NAME</td> <td>TERN.O.</td> <td>QTY.</td> <td>MATERIAL</td> <td>FINISHING</td> <td>REMARK</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td>DATE</td> <td colspan="4"></td> </tr> <tr> <td>DRAWN</td> <td>J.X.Zhang</td> <td>2013/11/11</td> <td colspan="4">ELECTRONICS CO.,LTD</td> </tr> <tr> <td>CHECKED</td> <td></td> <td></td> <td colspan="4">TITLE: PHONE JACKES</td> </tr> <tr> <td>APPROVALS</td> <td></td> <td></td> <td colspan="4">PART NO. DC-072</td> </tr> <tr> <td colspan="2">TOLERANCES ARE</td> <td>30[±] 0.15</td> <td>±0.30</td> <td>ANGLE</td> <td>UNIT: mm</td> <td>SCALE: 1:1</td> </tr> <tr> <td></td> <td></td> <td>10[±] 0.30</td> <td>±0.20</td> <td></td> <td></td> <td>PROJ. </td> </tr> <tr> <td></td> <td></td> <td>5[±] 0.10</td> <td>±0.15</td> <td>±Z'</td> <td>DRAWING NO.</td> <td>SHEET 1 OF 1</td> </tr> </table>							② Terminal	3	Phosphor bronze	Au Plating	① Housing	1	Nylon	Black	ITEM	PART NAME	TERN.O.	QTY.	MATERIAL	FINISHING	REMARK	APPROVALS		DATE					DRAWN	J.X.Zhang	2013/11/11	ELECTRONICS CO.,LTD				CHECKED			TITLE: PHONE JACKES				APPROVALS			PART NO. DC-072				TOLERANCES ARE		30 [±] 0.15	±0.30	ANGLE	UNIT: mm	SCALE: 1:1			10 [±] 0.30	±0.20			PROJ.			5 [±] 0.10	±0.15	±Z'	DRAWING NO.	SHEET 1 OF 1
② Terminal	3	Phosphor bronze	Au Plating																																																																			
① Housing	1	Nylon	Black																																																																			
ITEM	PART NAME	TERN.O.	QTY.	MATERIAL	FINISHING	REMARK																																																																
APPROVALS		DATE																																																																				
DRAWN	J.X.Zhang	2013/11/11	ELECTRONICS CO.,LTD																																																																			
CHECKED			TITLE: PHONE JACKES																																																																			
APPROVALS			PART NO. DC-072																																																																			
TOLERANCES ARE		30 [±] 0.15	±0.30	ANGLE	UNIT: mm	SCALE: 1:1																																																																
		10 [±] 0.30	±0.20			PROJ.																																																																
		5 [±] 0.10	±0.15	±Z'	DRAWING NO.	SHEET 1 OF 1																																																																