


ROHS

NOTE:
 1.Rating: 24V 25mA DC
 2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
 3.Withstand voltage: AC 500V 1Minute
 4.Operating Force Range: 1000gf Max
 5.Electrical Life: 2,000 Cycles
 6.Operating Temperature range $-20^{\circ}\sim +70^{\circ}\text{C}$
 7.Ambient Humidity used: $\leq 85\% \text{RH}$



Position(位数)		1P
PART NO.	凸柄(P)	DP-01RP
盖子/红色(R)	短柄(S)	DP-01RS
PART NO.	凸柄(P)	DP-01BP
盖子/蓝色(B)	短柄(S)	DP-01BS

⑤	Gum Water	—	—	Epikote	Black	—
④	Terminal	—	2	Phosphor bronze	Au Plating	—
③	Base	—	1	PBT	Black	—
②	Cover	—	1	PBT	Red/Blue	—
①	Keystoke	—	1	PBT	White	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	LIUCAN	2021.3.18				
CHECKED				PART NO.	DP-01□□	
APPROVALS				TOLERANCES ARE	ANGLE	UNIT: mm SCALE: 1:1 PROJ:
		30~以上	±0.30	±2'	DRAWING NO.	SHEET 1 OF 1
		10~30	±0.20			
		5~10	±0.15			
		~ 5	±0.10			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			