







ROHS



NOTE:
 1.Rating: 24V 25mA DC
 2.Insulation Resistance: ≥100 MΩ
 3.Withstand voltage: AC 500V 1Minute
 4.Operating Force Range: 1000gf Max
 5.Electrical Life: 2,000 Cycles
 6.Operating Temperature range -20°~+70°C
 7.Ambient Humidity used: ≤85%RH

Position(位数)	2P	3P	4P	5P	6P	7P	8P	9P	10P	12P	
DIM.A(长度)	6.64	9.18	11.72	14.26	16.80	19.34	21.88	24.42	26.96	32.04	
DIM.B(长度)	2.54	5.08	7.62	10.16	12.70	15.24	17.78	20.32	22.86	27.94	
PART NO.	凸柄(P)	DS-02RP	DS-03RP	DS-04RP	DS-05RP	DS-06RP	DS-07RP	DS-08RP	DS-09RP	DS-10RP	DS-12RP
盖子/红色(R)	短柄(S)	DS-02RS	DS-03RS	DS-04RS	DS-05RS	DS-06RS	DS-07RS	DS-08RS	DS-09RS	DS-10RS	DS-12RS
PART NO.	凸柄(P)	DS-02BP	DS-03BP	DS-04BP	DS-05BP	DS-06BP	DS-07BP	DS-08BP	DS-09BP	DS-10BP	DS-12BP
盖子/蓝色(B)	短柄(S)	DS-02BS	DS-03BS	DS-04BS	DS-05BS	DS-06BS	DS-07BS	DS-08BS	DS-09BS	DS-10BS	DS-12BS

⑤	Gum Water	—		Epikote	Black	—
④	Terminal	—		Phosphor bronze	Au Plating	—
③	Base	—	1	PBT	Black	—
②	Cover	—	1	PBT	Red/Blue	—
①	Keystoke	—	1	PBT	White	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	LIUCAN	2021.3.19				
CHECKED				TITLE:	MULTIFUNCTIONAL SWITCHES	
APPROVALS				PART NO.	DS-□□□□	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	±0.20				
	5~10	±0.15	±2'	DRAWING NO.		SHEET 1 OF 1
	~ 5	±0.10				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			