



■ 技术参数 SPECIFICATIONS

- ◆ 适用线规：AWG#28~#32
- ◆ Applicable Wire: AWG#28~#32
- ◆ 额定电压：125V DC,AC(rms)
- ◆ Rated voltage: 125V DC,AC(rms)
- ◆ 额定电流：1A
- ◆ Rated Current: 1A
- ◆ 耐压值：500V AC/minute
- ◆ Withstand voltage: 500V AC/min.
- ◆ 工作温度：-25°C ~ +85°C
- ◆ Working Temp：-25°C ~ +85°C
- ◆ 绝缘电阻：≥1000 MΩ
- ◆ Insulation resistance: ≥1000 MΩ
- ◆ 接触电阻：≤20mΩ
- ◆ Contact resistance: ≤20mΩ

DIM. Poles	DIM A	DIM B	DIM C
2	4.25	3.05	1.25
3	5.50	4.30	2.50
4	6.75	5.55	3.75
5	8.00	6.80	5.00
6	9.25	8.05	6.25
7	10.50	9.30	7.50

DIM. Poles	DIM A	DIM B	DIM C
8	11.75	10.55	8.75
9	13.00	11.80	10.00
10	14.25	13.05	11.25
11	15.50	14.30	12.50
12	16.75	15.55	13.75
13	18.00	16.80	15.00

DIM. Poles	DIM A	DIM B	DIM C
14	19.25	18.05	16.25
15	20.50	19.30	17.50
16	21.75	20.55	18.75

P.C.B Layout

②	PIN	—	Phosphor bronze	Ag-PLATED		
①	Base	—	PA46	Thermoplastic		
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS						
DRAWN		DATE		ELECTRONICS CO.,LTD		
JIANKUN.LU		2015.03.17				

CHECKED		TITLE:	
		Bar Connector Series	
APPROVALS		PART NO.	
		1.25T-1P-WP	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE						
30~0.15		±0.30		ANGLE		PROJ.
10~0.30		±0.20		UNIT: mm		SCALE: 1:1
5~10		±0.15		±2'		DRAWING NO.
~5		±0.10				SHEET 1 OF 1