



CIRCUIT DIAGRAM

Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:-20℃~70℃  
 Operating force:3-20N  
 Operating Life:5,000cycles

P.C.B LAYOUT  
 STAND OFF AREA

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

② Terminal	6	Phosphor bronze	Au Plating			
① Housing	1	Nylon	Black			
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE				
DRAWN	xu qi feng	2014.11.26	ELECTRONICS CO.,LTD			
CHECKED			TITLE: PHONE JACKES			
APPROVALS			PART NO. PJ-613			
TOLERANCES ARE		30~10.75	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
	10~30	±0.20				PROJ-4
	5~10	±0.15	±2'	DRAWING NO.		SHEET 1 OF 1