


ROHS



NOTE:
1. Operating force: 200±50gf

⑤	Teflon Films	—	1	—	—	—
⑤	Knob	—	1	NYLON	Black	—
④	Cover	—	1	SUS	—	—
③	Base	—	1	LCP	Black	—
②	Contact Clip	—	4	PBS C5210R-EH	Ag Clad	—
①	Terminal	—	12	Brass Strip	Ag Plated	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD													
DRAWN	J.X.Zhang	2014/09/11					TITLE:	TOGGLE SWITCHES									
CHECKED							PART NO.	K3-2268S-F1									
APPROVALS							TOLERANCES ARE	<table border="1"> <tr> <td>30~以上</td> <td>±0.30</td> <td rowspan="4">ANGLE</td> <td rowspan="4">UNIT: mm</td> <td rowspan="4">SCALE: 1:1</td> <td rowspan="4">PROJ: </td> </tr> <tr> <td>10~30</td> <td>±0.20</td> </tr> <tr> <td>5~10</td> <td>±0.15</td> </tr> <tr> <td>~ 5</td> <td>±0.10</td> </tr> </table>	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:	10~30	±0.20	5~10
30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:												
10~30	±0.20																
5~10	±0.15																
~ 5	±0.10																
DRAWING NO.		—		SHEET 1 OF 1													

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.