





ROHS



Schematic(Shorting)



P.C.B layout

NOTE:  
1. Operating force: 230±50gf

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Knob	—	1	NYLON	Black	—
④	Cover	—	1	SUS	—	—
③	Base	—	1	PA66	Black	—
②	Contact Clip	—	2	PBS C5210R-EH	Ag Clad	—
①	Terminal	—	10	Brass Strip	Ag Plated	—

APPROVALS		DATE		HRO 韓線 ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2018/08/01		TITLE:	TOGGLE SWITCHES	
CHECKED				PART NO.	K3-2410S-F1	
APPROVALS				UNIT: mm	SCALE: 1:1	PROJ:
TOLERANCES ARE	30~以上 ±0.30 10~30 ±0.20 5~10 ±0.15 ~ 5 ±0.10	ANGLE	±2'	DRAWING NO.		SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			