



ECN NO.


DATE.

REV.


## 动作方向








PCB LAND DIMENSION







2. 绝缘电阻:≥100ΜΩ

3. 耐电压: AC100V 50Hz/1min

CHANGE.

CHECK.

4. 电器寿命: 50000次

5. 环境温度:-10° ~+60°

6. 相对湿度:40℃ ≤95%


7. 接触电阻:≤1Ω

8. 接触行程:0.5±0.2

9. 动作力:≤26gf



CIRCUIT DIAGRAM



NEW DESCRIPTION.

5	Contact Spring		1	Phosphor bronze	Ag Plated		
4	Terminal		4	Brass	Ag Plated		
3	Base		1	LCP	Black		
2	Cover		1	SUS	Natural		
1	Knob		1	PA	Black		
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	

	APPR	D	ATE	NDDSE®			
	DRAWN	LIUCAN	202	1.3.3	ELECTRONICS CO.,LTD		
	CHECKED				TITLE:	DETECTOR	SWITCHS
	APPROVALS				PART NO.	K5-1673SA-01	
	TOLERANCES A	30~以上 RF 10~30	±0.30 ±0.20	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
APPRO.	TOLLIUMOLS A	5~10	±0.15	±2°	DRAWING NO.		SHEET 1 OF 1