



PIN=Ø1.0	
PIN=Ø1.3	
PIN=Ø1.65	

Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:-20℃~70℃  
 Operating force:3-20N  
 Operating Life:5,000cycles

②	Terminal	4	Phosphor bronze	Au Plating		
①	Housing	1	Nylon	Black		
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2013/11/11				
CHECKED				TITLE:	PHONE JACKES	
APPROVALS				PART NO.	DC-033	
TOLERANCES ARE			ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
30~以上	±0.30	±2'	DRAWING NO.	SHEET	1 OF 1	
10~30	±0.20					
5~10	±0.15					
~ 5	±0.10					

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.