



Circuit Diagram



PCB Layout(Pattern side)



PART NO		NO.1	
A	4.3	O	H
B	4.5	P	11
C	5	Q	11.5
D	5.5	R	12
E	6	S	12.5
F	6.5	T	13
G	7	U	13.5
H	7.5	V	14
I	8	W	15
J	8.5	X	16
K	9	Y	17
L	9.5	Z	18
M	10		19
N	10.5		15.5

NO.2	
PART NO	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	2	Brass(0.30t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	Plating silver	—
③	Base	—	1	Nylon	Black	—
②	Cover	—	1	SPCC	Plating Nickel	—
①	Keystroke	—	1	Nylon	Black	—

APPROVALS	DATE	TITLE:
DRAWN J.X.Zhong	2013/5/28	TACT SWITCHS

APPROVALS	PART NO.	SCALE:	PROJ.
CHECKED	K2-1102DE-□□SW-□□	1:1	□□□□
APPROVALS			
TOLERANCES ARE	30~以上 ±0.30	ANGLE	
	10~30 ±0.20	UNIT: mm	
	5~10 ±0.15	DRAWING NO.	
	~5 ±0.10		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			