



Circuit diagram

PCB Layout recommended

NO.1	
PART NO.	VIGOR
3	180±35
4	250±35

NO.2	
PART NO	MATERIAL/QTY
S	SUS/1PC

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	2	Phosphor Bronze	Plating silver	—
④	Contact	—	2	F.Ag/SUS	Natural	—
③	Base	—	1	LCP	White	—
②	Cover	—	1	Brass(0.20t)	Plating Nickel	—
①	Keystroke	—	1	LCP	Black	—

APPROVALS		DATE
DRAWN	JKUN,LU	2018.8.1

CHECKED		TITLE:	
APPROVALS		TACT SWITCHS	
TOLERANCES ARE		PART NO.	K2-1112SQ-ADDW-□□
30~0.1	±0.30	SCALE:	1:1
10~0.30	±0.20	UNIT:	mm
5~10	±0.15	ANGLE	±2°
~5	±0.10	DRAWING NO.	—



ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—