


Recommended PCB Layout



SPECIFICATIONS

1.RATING: DC30V 1.0A
2.MECHANICAL LIFE: 10,000 CYCLES.

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING
③	Base	—	1	NYLON	White
②	Terminal	—	4	Phosphor Bronze	Ag Plated
①	Housing	—	1	SPCC/Phosphor Bronze	Ni Plated

APPROVALS	DATE	TITLE:
DRAWN	JIANKUN.LIU	2018.08.01
CHECKED		USB CONNECTOR
APPROVALS		U-A-24DD-W-5

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

TOLERANCES ARE	30~80μm	±0.30	ANGLE	PART NO.	SCALE: 1:1	PROJ:
10~30	±0.25			U-A-24DD-W-5		
5~10	±0.20	±2°				
~5	±0.15					



ELECTRONICS CO.,LTD