



规格说明: Specifications:
电气特性: Electrical:

- 1. 额定电流: Current Rating
1.5A/contact terminal
- 2. 额定电压: Voltage Rating

物理性能: Mechanical:

- 1. 插拔力: Connector Mate and Umate Force
Mate force: 3.57kgf(MAX)
Umate force: 1.02kgf(MIN)
- 2. 端子保持力: Terminal Retention
1.0kgf(MIN)

③	Base	—	1	NYLON	White/Black
②	Terminal	—	4	Phosphor Bronze	Ag Plated
①	Housing	—	1	SPCC/Phosphor Bronze	Ni Plated
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING

APPROVALS		DATE	TITLE: USB CONNECTOR		
DRAWN		JIANKUN LU	ELECTRONICS CO.,LTD		
CHECKED		2018.08.01			
APPROVALS					

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.				
	A		NEW							
TOLERANCES ARE		30~以上 ±0.30	10~30 ±0.25	5~10 ±0.20	~5 ±0.15	ANGLE ±2°	UNIT: mm	SCALE: 1:1	PROJ:	SHEET 1 OF 1