







5	6
REV.	ECN NO OR DESCRIPTION
REVISED	DATE



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CCI	B8	SBU2
A6	DPI	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

備注:

1. 材質:

- 1.1 端子: C5191R-EH, T=0.15mm.
- 1.2 胶芯: LCP+30%GF; 顏色: 黑色
- 1.3 外壳: SUS 304R-1/2H. T0.30mm

2. 电镀:

端子接触区镀金3U", 焊接区镀锡
外壳表面镀镍100μ"

3. 电压: 5V AC MAX.

4. 电流: 3A

5. 插入力: 35N MAX

拔出力: 10N MIN. INITIAL 8-20N AFTER

6. 耐久性: 10000 CYCLES MIN

7. 耐电压: 100V AC.

8. 接触阻抗: 40mΩ MAX.

9. 绝缘电阻: 1000mΩ MIN.

10. 工作温度: -40度 TO +70度 .

11. 盐雾:


11.1 端子: 48H

11.2 外壳: 24H

12. 耐温:

12.1 LCP 胶芯: 260±5℃

12.2 端子耐焊性: 260±5℃



UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS: X :±0.5 X.X :±0.20 X.XX :±0.10		ANGLES: X :±2° X.X :±1°		TITLE TYPE C16P 四脚全贴 无弹	
DWN	xiong	PART NO. MC-307			
CHKD	lee	SCALE: 1:1	UNIT: mm		
APVD	wang	SIZE: A4	SHEET: 10F 1	REV: A4	
CUSTOMER COPY					