



Model No.	DC-087
Schematic	

Rating: 3A 30V DC
 Contact Resistance: 30 mΩ Max.
 Operating temperature: -20℃~70℃
 Operating force: 3-20N
 Operating Life: 5,000cycles

Model No.	1	2	3
PIN	∅1.65	∅2.0	∅2.5

②	Terminal	1	Brass	Sn Plating		
①	Housing	1	PBT	Black		
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD			
DRAWN	LIUCAN	2020.12.10					
CHECKED				TITLE:	PHONE JACKES		
APPROVALS				PART NO.	DC-087		
TOLERANCES ARE		30~以上 ±0.30	10~30 ±0.20	ANGLE	UNIT: mm	SCALE: 1:1	
		5~10 ±0.15	~ 5 ±0.10	±2'	DRAWING NO.		
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	PROJ:

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			